



4-FIL Blank Plate Installation Sheet



Description

The 4-FIL Blank Plate is used to cover one slot in the UI frame assembly when no user interface module is installed.


Installation

Install this device in accordance with applicable national and local codes, ordinances, and regulations.

To install the 4-FIL:

1. Attach the blank plate on the inner door UI frame assembly by inserting the tabs on the bottom of the blank plate into the slots at the bottom of the frame assembly.
2. Push the top of the blank plate toward the frame assembly until the locking tab at the top of the plate snaps and locks into place on the frame assembly. See Figure 1.

Figure 1: 4-FIL blank plate installation



- (1) Inner door (outer door removed for clarity)
- (2) UI frame assembly
- (3) 4-FIL Blank Plate
- (4) Tab on bottom of blank plate
- (5) Mounting clip at top of blank plate

Specifications

Operating environment	
Temperature	32 to 120°F (0 to 49°C)
Relative humidity	0 to 93% noncondensing

Regulatory information

Note: For other regulatory information, refer to *EST4 European Marketplace Manual* (P/N 3102838).

Environmental class	UL/ULC: Indoor dry IEC: 3K5
---------------------	--------------------------------

Contact information

For contact information, see www.edwardsfiresafety.com.

